



Vacuum Press V.4000

*Vacuum-press for manufacturing of soles and foot-orthotics.
In sole production, it is produced individually. It is used with low vacuum.
vacuum starts manually, discharging is done manually at the end of the process.*

Technical Data

Product Code
Dimensions
Capacity
Vacuum
Vacuum
Accessories
Weight Net
Boxed : Dimension and Total Weight

Descriptions

V.4000 Manual Mechanical adjustment
W.60 D.67 H.10 cm
3 m³/200 mbar
Vacuum On
Vacuum off
1 Pcs Hose 4 mt
16 Kg
W.70 -D.80- H.20 cm 20 kg