

Orthopedic workshop Machine



Electric Silicone Roller SLM.5000

For mixing larger quantities of silicone [up to 3 kg], rolling them into large silicone sheets with thicknesses ranging from 0.1 to 35 mm and sizes up to max.650 mm, manual processing of highly viscous HTV silicones.

Technical Data

Product Code Dimension Power Supply Power cord Version

Equipment Electrical Connection Control Systems Safety Systems Roll Dimension diameter xL Roll gap Roll speed Type of planning and Equipment Color and Material Weight Net Boxed : Dimension and Total Weight

Descriptions

SLM.5000

W.128-D.65-H.125 cm 220 Volt 50-60 Hz With CEE plug 3 × 16 A and CEE socket 3 × 16 A Safety concept according to EN 12301 standard, safety featuresbcorrespond to category 4 Hazard Buttons ,Foot pedal 220 Volt 50-60 hz 2.200 Watt **Automatic Digital Systems Electrical and Mechanical** 200 x 750 mm 0.1 to 35 mm 0-20 RPM Slicone processing RAL 7035 and 7045 steel 498 Kg W.145 - D.800 – H155 cm / 595 kg

Page.10

www,ortomak.com ortomak@ortomak.com